A 100% DUALOPTIX™ DIGITAL FAMILY OF PRODUCTS



The right product for your customers

| | DEFINITY ® | DEFINITY 3 | DEFINITY 3 PLUS |
|---|-------------------|------------|-----------------|
| | STANDARD | CUSTOMIZED | PERSONALIZED |
| Computer automatically selects between Regular and Short design | | ~ | |
| Fixed split of the ADD: +0.75 on the back, remaining ADD power on the front | V | | |
| Dynamic split of the ADD individually tailored to the patient's Rx | | V | / |
| Optimized to frame choice with A, B, PD, & Seg Height fitting measurements | | ✓ | / |
| Incorporates 3 additional fitting parameters for a personalized fit: | | | V |

Keep your patients satisfied as presbyopia progresses, with quite possibly the only PAL they'll ever need

- 35% less unwanted astigmatism vs competing PALs
- 4 out of 5 patients adapt immediately
- Outperforms the competition, especially at high ADD powers
- Performs better in all visual zones than DEFINITY lenses
- Easy to order

Panto, Wrap and Vertex

Discover a distinctively different experience with DEFINITY—unique designs, superior support and an unparalleled community of dispensers. Visit **definitycommunity.com/D3.**





DEFINITY® DIGITAL LENSES—AVAILABILITY CHART

NEW

DEFINITY® 3 PLUS

Minimum fitting height: 15mm. Max Ground View Advantage[™] benefits at fitting heights ≥ 19mm

| Material | 1.50 Plastic | TREXA™ | Airwear® | Thin&Lite® | | |
|---------------------------------|-----------------|-----------------|-----------------|---------------|-----------------|---------|
| | | | | 1.60 | 1.67 | 1.74¹ |
| Power Range | +6.00 to -10.00 | +6.00 to -10.00 | +6.00 to -10.00 | Not Available | +9.00 to -12.00 | Q1 2013 |
| Cylinder | up to -6.00 | up to -6.00 | up to -6.00 | | up to -6.00 | |
| ADD Power | +1.00 to +3.50 | +1.00 to +3.50 | +1.00 to +3.50 | | +1.00 to +3.50 | |
| LENS OFFERINGS | | | | | | |
| Crizal® No-Glare technologies 2 | • | • | • | Not Available | • | Q1 2013 |
| Optifog™ 3 | • | • | • | | • | |
| Transitions® VI Lenses | Gray & Brown | Gray & Brown | Gray & Brown | | Gray & Brown | |
| Xperio® Polarized 4 | N/A | N/A | Gray | | N/A | |

NEW

DEFINITY® 3

Minimum fitting height: 15mm. Max Ground View Advantage benefits at fitting heights ≥ 19mm

| Material | 1.50 Plastic | TREXA™ | Airwear® | Thin&Lite® | | |
|--|-----------------|-----------------|-----------------|---------------|-----------------|---------|
| | | | | 1.60 | 1.67 | 1.74¹ |
| Power Range | +6.00 to -10.00 | +6.00 to -10.00 | +6.00 to -10.00 | Not Available | +9.00 to -12.00 | Q1 2013 |
| Cylinder | up to -6.00 | up to -6.00 | up to -6.00 | | up to -6.00 | |
| ADD Power | +1.00 to +3.50 | +1.00 to +3.50 | +1.00 to +3.50 | | +1.00 to +3.50 | |
| LENS OFFERINGS | | | | | | |
| Crizal® No-Glare technologies ² | • | • | • | Not Available | • | Q1 2013 |
| Optifog™ ³ | • | • | • | | • | |
| Transitions® VI Lenses | Gray & Brown | Gray & Brown | Gray & Brown | | Gray & Brown | |
| Xperio® Polarized 4 | N/A | N/A | Gray | | N/A | |

DEFINITY® / DEFINITY SHORT™

Regular: min fitting height: 18mm. Max Ground View Advtange benefits at fitting heights ≥ 22mm Short corridor: min fitting height: 15mm. Max Ground View Advantage benefits at fitting heights ≥ 19mm

| Material | 1.50 Plastic | TREXA™ | Airwear® | Thin&Lite® | | |
|--|-----------------|-----------------------|----------------|-----------------|-----------------------|-----------------|
| | | | | 1.60 | 1.67 | 1.74¹ |
| Power Range | +6.00 to -10.00 | +6.00 to -10.00 | +4.00 to -7.00 | +8.00 to -12.00 | +10.00 to -12.00 | +9.00 to -14.00 |
| Cylinder | up to -4.00 | up to -4.00 | up to -4.00 | up to -4.00 | up to -4.00 | up to -4.00 |
| ADD Power | +1.00 to +3.00 | +1.00 to +3.50 & 4.00 | +1.00 to +3.00 | +1.00 to +3.00 | +1.00 to +3.50 & 4.00 | +1.00 to +3.50 |
| LENS OFFERINGS | | | | | | |
| Crizal® No-Glare technologies ² | • | • | • | • | • | • |
| Optifog ^{™ 3} | • | • | • | • | • | N/A |
| Transitions® VI Lenses | Gray & Brown | Gray & Brown | Gray & Brown | N/A | Gray & Brown | N/A |
| Xperio® Polarized 4 | Grav & Brown | N/A | Grav & Brown | N/A | N/A | N/A |



DEFINITY Thin&Lite 1.74 lenses will systematically include a Crizal No-Glare technology

Please reference the full Crizal availability chart available at www.crizalusa.com Please reference the full Optifog availability chart at www.optifogusa.com

Crizal SunShield UV™ is recommended with every DEFINITY Xperio job. Power ranges vary for Xperio—check with your lab for availability